

LED 10W LAMP WITH TOUCH MODES

User Manual



Five dimming options



3 colour options in "M" mode with touch modes, easy functionality



Foldable design
Adjustable to various angles



Anti-radiation



50000 Hours



Green" light



Energy saving




Plastic LED cover in matt for eye protection


Warnings



Do not repair, disassemble, or modify under any circumstances.




Do not place near any heat source or in direct sunlight.



Please insure that lamp is placed on a straight and safe desktop or platform.



AC power adaptor
OUTPUT : DC 5V -- 2A




Do not use LED lamp with frayed or damaged electrical cords.



Do not touch LED lamp or electrical plug when hands are wet or near liquids.



Ensure LED lamp parts are always dry and away from humidity.



Unplug adaptor when the LED lamp will not be used for an extended time.



Clean only with a soft dry cloth and do not use solvents or diluted liquids.




Gently press the digital buttons without using pressure.


Specifications

MODEL	PTL003		
Colour of equipment	White	CRI	> 80
Light temperature	2800K - 5500K	Material	ABS + Metal
LEDs duration	50.000 Hours	Warm light	2800K-3300K
Power	10 W	Natural light	4000K-4500K
Voltage	110V - 240V	Cold light	5000k-5500K
Input	DC5V, 2A	Switch	Touch
Weight	672 gr	Adapter	US/EU/UK/AU
Lux	1000 Lux	LED Quantity	40pcs SMD
Dimensions	150 mm (L) * 340 mm (H) * 390 mm (W)		


Instructions



1. Apply the AC input of the adapter to the socket found on the back of the LED lamp, indicated by letter A.



2. Touch the symbol indicated by the letter B to switch LED lamp on or off (refer to the operating instructions for more details).



Adjustable angle of the lamp arm:

- When adjusting the top arm with the LEDs lights, hold the base.
- Upper arm adjusts 180° with 90° rotation to the left or right. Do not excessively force when rotating in order not to cause damage.
- Lower arm connected to base, adjusts 90°.



WARNING:

1. Although the LED lamp has eye protection, do not stare at LED lamps.
2. This lamp is not repairable, due to the parts and labour being more expensive than the value of the equipment.


WARRANTY

1. 6 months.
2. The warranty period starts from the date of invoice.

Key functions

M ⏻ + -
1 2 3 4

- 1 - Press the "M" key for 3 colour temperature options - Cold light, Warm light or Natural light.
- 2 - Touch 2nd key "POWER" to turn LED Lamp ON or OFF.
- 3 - Increase brightness.
- 4 - Decrease brightness.



Luís Abreu Pestana, Cosmética, Lda.

Rua António Oliveira, nº40, Loja AM, Centro Empresarial do Oeste, Zona Industrial; 2500-916 Caldas da Rainha - Portugal
Telephone: +351 262889070 Email: encomendas@lpcosmetica.pt www.lpcosmetica.pt / www.lpcosmetica.com